S.HOWES

Granulator

Sample Applications:

- Corn
- Salt
- Wheat
- Barley
- Milo
- Beans
- Peanuts
- Resin
- Mustard
- Charcoal
- Pigmentt

Testing & Rental Units Available!




For more information contact one of our Sales Engineers sales@showes.com www.showes.com S. Howes. Inc. Phone: (716) 934-2611 Toll Free: (888) 255-2611 Fax: (716) 934-2081 © 2014 S. Howes, Inc. All rights reserved

DESCRIPTION

The S. Howes Granulator is built with heavy duty iron castings and a tubular steel frame. The interior of the granulator has a replaceable wear plate, collar and seal in the upper mechanism.

The feed spout consists of an adjustable slide gate to regulate product flow into the Granulator.

The material is cut between the offset rings that rotate at approximately the same speed. Centrifugal action forces the material outward between the cutter rings which shear it to size and eject it immediately. This unique action creates less fines and a clean sharp product.



S. Howes, Inc. 25 Howard St. Silver Creek, NY 14136 **showes.com**

Phone: (716) 934-2611 Toll Free: (888) 255-2611 Fax: (716) 934-2081 sales@showes.com

